



IR400P5 Multipurpose Station

IL900 Specification Sheet

Tek-CARE®400 P5 Nurse Call System • Rev. 2 - 08/2015

Features

- UL® 1069 Listed and cUL® Listed
- Control and power over CAT5 cable
- Fully supervised wiring to the central equipment
- All stations are interchangeable
- Simplified wiring with plug-in connectors
- Designed for cleanability
- Half-duplex and full-duplex audio options

Description

The IR400P5 Multipurpose Station provides audible, visual and digital communications to and from the Tek-CARE®400 central equipment (CE) when receiving or sending signals to remotely connected devices.

The IR400P5 includes inputs for contact closures and all types of emergency call switches for these systems. It also provides an output to a speaker or paging amplifier, and a corridor lamp. It does not have the controls, LEDs or speakers normally associated with patient, staff or duty stations.

Some practical applications for the IR400P5 are to provide: input for code emergency call stations in an ICU; a PA amplifier interface for the nurse call master; an alarm input point for exit/entry doors and narcotics cabinets; input for bath emergency call stations in public bath areas; or input to a remote door intercom station for access control.

Listings



UL® 1069 listed and cUL® listed to CSA C22.2 No. 205; UL® File Number E71599.



IR400P5 Multipurpose Station

Specifications

Dimensions:	Height:	4.5"	(114 mm)
	Width:	7.0625"	(179 mm)
	Depth:	up to 2.5"	(64 mm)
	Projects:	0.5"	(12.7 mm)
Construction:	Flame-retardant (UL® 94V-0) plastic		
Connections:	Plug-in connectors for peripherals		
Housing:	RACO 692, or Steel City #H3BD with Steel City #3GC plaster ring, or exact equal. Conduit access for masonry boxes must be through the top.		
Wiring:	Control and power over CAT5 or better cable.		

Required Components

- Tek-CARE®400 P5 nurse call system
- PM455 Master & Station Module
- SF300-series peripheral switches

www.tektone.com

277 Industrial Park Road • Franklin, NC 28734 • tektone@tektone.net

Phone: (828) 524-9967 • Fax: (828) 524-9968 • Sales: Choose option 2 • Tech Support: Choose option 3
TekTone®'s quality system is registered by UL® to the ISO 9001 standard. (Reference #10001510.)